



Knowledge Beyond Measure.

PortaCount® Respirator Fit Tester

Model 8048



Respirator Fit Testing You Can Trust

PortaCount® Respirator Fit Tester utilizes the most effective quantitative fit testing method available to identify poor fitting masks. Industry-first features train staff how to wear respirators for optimal protection. Have confidence with the most trusted fit test instrument to increase your staff's safety, and improve your program's efficiency and productivity.

Features and Benefits

- OSHA, CSA, HSE INDG, ANSI/ASTM, ISO, INRS and JIS accepted for ALL Full-facepiece and Half-facepiece tight fitting elastomeric respirators and filtering facepiece respirators, including NIOSH Series -95 /-99 /-100; EN -P1 / -P2 / P3 filter media.
- Measures fit factors from 1 to greater than 10,000
- Computes respirator fit factor using microscopic particles in ambient air
- Automates fit testing with FitPro™ Ultra Software
- Real-Time FitCheck™ Mode to train new users and troubleshoot failed fit tests
- Mask sampling adapter kits enable fit testing in employee's personal respirators
- Software can print fit test cards with fit test report

PortaCount® Model 8048 Includes

- N95-Companion™ Technology
- Carrying case
- AC adaptor
- Alcohol supply (sixteen 30 ml bottles of 99.5% reagent grade isopropanol – enough for ~240 hours of operation)
- FitPro™ Ultra Fit Test Software
- Particle Generator
- Standard accessory kit (twin tubing, zero filters, spare wicks, alcohol fill capsule and cartridge, USB cable)
- Filtering Facepiece fit testing kit (probe insertion tool, probes, push nuts and lanyard)

FitPro™ Ultra Fit Test Software

- New FitPro™ Ultra Fit Test Software improves efficiency and simplifies fit testing
- New advanced user interface with intuitive design supporting one-step-to-a-fit test
- Wireless WiFi® communication to leverage the utility of a laptop or tablet
- Industry first active animations guide the test subject through the fit test exercises to ensure greater compliance
- Interactive troubleshooting guide



Air-Met Scientific

1800 000 744

sales@airmet.com.au

www.airmet.com.au



Specifications

PortaCount® Respirator Fit Tester

Model 8048

Fit Factor Range

1 to greater than 10,000, 1 to 200 for respirators with <99% efficient filters (i.e., N95's)

Respirator Facepieces that can be Fit Tested

Full-facepiece elastomeric
Half-facepiece elastomeric
NIOSH Series-100 filtering-facepiece
NIOSH Series-99 filtering-facepiece
NIOSH Series-95 filtering-facepiece
EN FFP1 filtering-facepiece
EN FFP2 filtering-facepiece
EN FFP3 filtering-facepiece

Fit Factor Measurement

Direct measurement of fit factor = $(C_{out}/C_{in})^*$

Dimensions

4.83 in. x 10.5 in. x 9.46 in. (12 cm x 27 cm x 24 cm)

Weight

Unit Only	7.0 lb. (3.2 kg)
With Standard Accessories and Case	15.35 lb. (6.9 kg)

Power

Autosensing 100 to 250 VAC, 50 to 60 Hz

Flow Rate

Sample	350 cm ³ /min
Total	1000 cm ³ /min (nominal)

Temperature Range

Operation	32 to 100°F (0 to 38°C)
Storage	-40 to 122°F (-40 to 50°C)

Working Fluid

99.5% reagent grade isopropyl alcohol.

Run time per charge: Typical 6-hr of fit testing operation at 70°F (21°C)

Carrying Case

Dimensions (HWD) 10.0 in. x 20.5 in. x 15.5 in.
(25.4 cm x 52.1 cm x 39.4 cm)

Pass/Fail Setting

User-selectable: 0 to 10,000

Factory Recalibration Interval

One year

Warranty

Two years on workmanship and materials.

Communications

WiFi, USB-C, USB-A

PC Hardware Requirements for FitPro™ Ultra Fit Test Software

Windows® 7 (32 and 64 bit), Windows® 8 (32 and 64 bit), Windows® 10, and Windows® 11 (32 and 64 bit) operating system Microsoft.
Net version 4 (installation software will install Microsoft.Net if necessary) Note — An internet connection is required to install Microsoft.Net.
≥ 1 GHz process
≥ 1280 x 800 screen resolution monitor
500 MB free space on hard drive
1 free USB port

Tablet Requirements

Windows® 10 and Windows® 11 operating system USB port (for initial set up)

Software

FitPro™ Fit Test Ultra Software featuring advanced user interface, animated graphics, and interactive troubleshooting guide.

Optional Accessories

Mask Sampling Adapters for select respirator models.
Microsoft® Surface Pro Tablet (4 GB RAM, 128 GB of storage).
WiFi USB dongle.

*Mask leakage is measured simultaneously while test subject moves and breathes.

Wi-Fi is a registered trademark of the Wi-Fi Alliance.

Windows and Microsoft are registered trademarks of Microsoft Corporation in the United States and/or other countries.

FitCheck, PortaCount, TSI and the TSI logo are registered trademarks of TSI Incorporated in the United States and may be protected under other country's trademark registrations.

To see our list of patents please visit:
www.tsi.com/patents



Knowledge Beyond Measure.

TSI Incorporated - Visit our website www.tsi.com for more information.

USA	Tel: +1 800 874 2811	India	Tel: +91 80 67877200
UK	Tel: +44 149 4 459200	China	Tel: +86 10 8219 7688
France	Tel: +33 1 41 19 21 99	Singapore	Tel: +65 6595 6388
Germany	Tel: +49 241 523030		