

- Protect workers, reduce false alarms, and spend less time managing your gas detector fleet with the Tango TX2.
- The Tango TX2 is the most accurate two-gas monitor featuring individual sensors that increase alarm accuracy.
- A two-year runtime and replaceable battery simplify gas detection management by eliminating the need for charging infrastructure.

INSTRUMENT CONFIGURATIONS

INCINCINE	CONTIGORATIONS
PART NUMBER	DESCRIPTION
TX2-12011	Tango TX2, CO, H ₂ S, English
TX2-14011	Tango TX2, CO, NO ₂ , English
TX2-15011	Tango TX2, CO, SO ₂ , English
TX2-1G011	Tango TX2, CO, CO Low , English
TX2-56011	Tango TX2,SO ₂ , NH ₃ , English
TX2-1B011	Tango TX2, CO, HCN, English
TX2-24011	Tango TX2, H ₂ S, NO ₂ , English
TX2-25011	Tango TX2, H ₂ S, SO ₂ , English
TX2-2G011	Tango TX2, H ₂ S, CO Low, English
TX2-45011	Tango TX2, NO ₂ , SO ₂ , English
TX2-4G011	Tango TX2, NO ₂ , CO Low, English
TX2-5G011	Tango TX2, SO ₂ , CO Low, English
TX2-6B011	Tango TX2, NH₃, HCN, English

ACCESSORIES

18109330 -ABC -ABC	DSX™ Docking Station for Tango® TX1 A − DSX Mode: 0 = DSX Standalone, 1 = DSXi Cloud-connected, 2 = DSX-L Local Server B − Number of Gas Inlet Ports: 3 = 3 Ports, 6 = 6 Ports C − Power Cord Type: 1 = North America, 2 = Europe, 3 = Australia, 4 = UK
17154367	Replacement battery
18109171	Soft nylon case, Black
18109239	Soft nylon case, Safety Orange
18109218	Dust barrier kit, 5 pack
18109230	Water barrier kit, 5 pack
18109238	CalCup and tubing kit
17154484	Suspender clip
17154915-0	AlarmAmp, Black
17154915-1	AlarmAmp, Safety Orange

- * These specifications are based on performance averages and may vary by instrument.
- ** Operating temperatures above 50 °C (122 °F) may cause reduced instrument accuracy. Operating temperatures below -20 °C (-4 °F) may cause reduced instrument accuracy and affect display and alarm performance.

Patent No. 9,000,910 - DualSense® Technology | Patent No. 9,064,386 - AlarmAmp®

INDUSTRIAL SCIENTIFIC

AMERICAS

Phone: +1-412-788-4353 1-800-DETECTS (338-3287) | info@indsci.com Guaranteed for Life[™]. Warranted for as long as the instrument is supported by Industrial Scientific Corporation (excludes sensors, batteries, and filters). CO and H₂S sensors are warranted for three years. All other sensors are warranted for two years.

DISPLAY

Segment liquid crystal display (LCD)

KEYPAD

Two buttons

CASE MATERIALS

Case top: Polycarbonate with a protective rubber overmold Case bottom: Conductive polycarbonate

ALARMS

Three strobe-emitting visual alarm LEDs (two red; one blue) 100 decibel (dB) audible alarm at a distance of 10 cm (3.94 in); Vibration alarm

DIMENSIONS

99 x 51 x 35 mm (3.9 x 2.0 x 1.4 in)

WEIGHT

126.0 g (4.4 oz)

TEMPERATURE RANGE

-40 °C to 50 °C (-40 °F to 122 °F) **

HUMIDITY RANGE

15% to 95% Non-condensing (continuous)

CO, CO/H₂, HCN, H₂S, NH₃ NO₂, SO₂ – Electrochemical sensor technology

SENSOR MEASURING RANGES

0 to 500 ppm in 1 ppm increments Ammonia (NH₂): Carbon Monoxide (CO): 0 to 1,000 ppm in 1 ppm increments 0 to 1,000 ppm in 1 ppm increments Carbon Monoxide (CO/H₂ low): Hydrogen Cyanide (HCN): 0 to 30 ppm in 1 ppm increments Hydrogen Sulfide (H,S): 0 to 500.0 ppm in 0.1 ppm increments Nitrogen Dioxide (NO₂): 0 to 150.0 ppm in 0.1 ppm increments Sulfur Dioxide (SO₂): 0 to 150.0 ppm in 0.1 ppm increments

BATTERY

3.6 V Primary lithium-thionyl chloride (Li-SOCI2); 1.5AH, 2/3AA; replaceable; non rechargeable; always on; up to 2-year run time depending on operating conditions

DATA LOGGING

3 months at 10-second intervals

EVENT LOGGING

60 alarm events

CERTIFICATIONS

DIRECTIVE OR CB AREA CLASSIFICATION STANDARDS

ATEX1: Ex ia I Ma;

Ex ia IIC T4 Ga; Equipment Group and Category: I M1 and II 1G,

EN 60079-0: 2012 EN 60079-11: EN 50303: 2000

Ex ia I Ma, Ex ia IIC T4 Ga

IEC 60079-0: 2011 IEC 60079-11:

Class I, Groups A, B, C, and D; Class II, Groups E, F, and G; T4; UL (C-US)4:

Exia Class I, Zone O, AEx ia IIC T4

UL 913 8th Ed. UL 60079-0 6th Ed. UL 60079-11 6th Ed. CSA C22.2 No. 157

ASIA PACIFIC

EMEA

Phone: +65-6561-7377 Phone: +33 (0)1 57 32 92 61 Fax: +65-6561-7787 | info@ap.indsci.com Fax: +33 (0)1 57 32 92 67 | info@eu.indsci.com

www.indsci.com

Rev 0624